## **Lab Edging Systems**

#### **SE-9090 Express Specifications**

Grinding System	Patternless					
	Double Spindle System					
Grinding Mode	Auto Grinding : Computer Beveling					
	Guided Grinding					
	Flat Edging					
	Safety Beveling (Chamfering)					
	Polishing (Type PLB only. Type PLA polishes safety-beveled edges. )					
Grinding Lens						
Material	Plastic (CR-39 etc.), Polycarbonate, Acrylic Resin, TRX (Type PLA or Type					
	PLB), Glass (Type GLS)					
Minimum Grinding Size						
With chamfering	When Flat Edging: 33 (Horizontal Width) x 26 (Vertical Width) mm					
	When Beveling : 35 (Horizontal Width) x 27 (Vertical Width) mm					
Without Chamfering	When Flat Edging: 33 (Horizontal Width) x 20 (Vertical Width) mm					
	When Beveling : 34 (Horizontal Width) x 21 (Vertical Width) mm					
Grinding Pressure	Variable: 7 Levels (Automatic Control by Program)					
Display	10.4 - inch SVGA Color Display (Touch Panel)					
Lends Chucking						
Chucking Method	Electric					
Chucking Pressure	Variable: 7 Levels (Parameter Setting)					
Water Supply System	Pump Circulation or Direct Connection to Tap Water					
Power Supply						
Power Source	AC200 - 240 V, 50/60 Hz (Single Phase)					
Power Consumption	2.5k VA					
Dimensions/Weight	600 (W)x510(D)x611(H) mm/120 kg					
	23.6(W)x 20 (D)x 24 (H) "/265 lbs.					
Standard Accessories	Lens Cup (x10), Lens Cup for Half-eye Lenses (x10), Double-coated Adhesive					
	Tape (x1 box), Lens Adapter/Lens Clamp for Half-eye Lenses (x1 set), Cup					
	Remover (x2), Coupler (x2), Hose Band (x2), Duct (x2), Duct Adapter (x2),					
	Power Cable, Monkey Wrench, Hex. Wrenches (2, 5, 6 mm), Dressing Stick					
	for Roughing Wheel :WA80 K (Type GLS only), Dressing Stick for Finishing					
	Wheel :WA320, Dressing Stick for Polishing Wheel :WA4000 (Except for Type GLS)					

#### **AHM-1000 Specifications**

Drilling	
Hole dia.	Dia. 0.8 - 3.0 mm (in increments of 0.1 mm)
Hole depth	6.0 mm or less
Drilling range	Dia. 33 - 70 mm around lens axis
Drilling direction	Normal to lens surface (max. 30°)
Grooving	
Width	0.6 - 1.2 mm continuously variable (in increments of 0.1 mm)
Depth	0.0 - 0.8 mm continuously variable (in increments of 0.1 mm)
Grooving mode	Automatic
	Guided
Display	10.4 - inch SVGA color LCD (Touch Panel)
Power Supply	
Power Source	AC200 - 240V, 50/60 Hz
Power Consumption	300 VA
Dimensions/Weight	400(W)x 515 (D)x 611 (H) mm/50 kg
	16 (W)x20.6(D)x24.4(H) "/110 lbs.
Standard Accessories	End mill (x10), Grooving cutter (x1), Lens Adapter/Lens Clamp for Half-eye
	Lenses (x1 set), Standard Pattern, Grooving Calibration Jig, Drill Calibration
	Jig, Coupler, Hose Band, Duct (1M), Duct Adapter, Power Cable, Monky
	Wrench (8 - 9 mm), Hex' Wrenches (2, 5, 6 mm), Fuse (x4), Interface Cable

#### RHU-1000 / 1500 Specifications

Conveyable Lens	
Outer dia. (Before Grinding)	80 mm dia. or Less
Outer dia. (After Grinding)	20 mm dia. or More
Maximum Thickness	17 mm (Edge of Concave Lens)
	10 mm (Center of Concave Lens)
	14 mm (Total of Convex Lens)
Power Supply	
Power Source	AC 200/230 V, 50/60 Hz (Single Phase)
Power Consumption	600 VA
Positive Pressure	
Used Fluid	Dry Air
Pressure Supply	0.45 - 0.8 MPa
Flow	70 L /min or More
Connection Method	10 mm dia. One-Touch Joint
Dimensions/Weight	
RHU-1000	800 (W)x 875 (D)x1472(H) mm/140 kg
	31.5(W)x 34.4 (D)x 58 (H) "/309 lbs.
RHU-1000S	800 (W)x1185(D)x1472(H) mm/220 kg
	31.5(W)x 44.3(D)x 58 (H) "/486 lbs.
RHU-1000CB	1207(W)x1128(D)x1472(H) mm/185 kg
	47.5 (W)x 44.4 (D)x 58 (H) "/ 408 lbs.
RHU-1500	1300(W)x1185(D)x1472(H) mm/230 kg
	51.2 (W)x 46.7 (D)x 58 (H) "/ 507 lbs.
Standard Accessories	RS-232C Cable, Drain Hose

<sup>\*</sup>Specifications and design are subject to change without notice for improvement.

#### VISIONARY PERFORMANCE



Printed on environment-friendly recycled paper.

Printed in Japan Lab Edging Systems NMDMM①

# **Lab Edging Systems**



#### HEAD OFFICE

34-14 Maehama, Hiroishi Gamagori, Aichi 443-0038, Japan Telephone : 81-533-67-6611 Facsimile : 81-533-67-6610 URL: http://www.nidek.co.jp

#### TOKYO OFFICE

(International Div.) 6F Takahashi Bldg., 3-2 Kanda-Jinboucho Chiyoda, Tokyo 101-0051, Japan Telephone: 81-3-3288-0571 Facsimile: 81-3-3288-0570

#### NIDEK INC.

47651 Westinghouse Drive Fremont, CA 94539, U.S.A. Telephone : 1-510-226-5700 : 1-800-223-9044 (US only) Facsimile : 1-510-226-5750 : http://www.nidek.com

#### NIDEK TECHNOLOGIES AMERICA INC.

Suite 101 Greensboro, NC 27410, U.S.A. Telephone : 1-336-851-0225 : 1-888-382-5064 (US only) Facsimile : 1-336-851-0917 : http://www.nidektech.com

#### NIDEK SOCIÉTÉ ANONYME Europarc

5500 West Friendly Ave.

13, rue Auguste Perret 94042 Créteil, France Telephone : 33-1-49 80 97 97 Facsimile : 33-1-49 80 32 08 : http://www.nidek.fr

#### NIDEK TECHNOLOGIES SRL. Via Regia, 88

35010 Vigonza (Padova), Italy Telephone : 39.049.8935287 / 8935191

Facsimile : 39.049.625584

: http://www.nidektechnologies.it









## **Complete Automation & Lens Processing**

Various configurations are made possible with NIDEK's Lab Equipment --- SE-9090 Express, AHM-1000 and RHU-1000/1500.

From a small optical lab to a large scale outfit, NIDEK delivers and provides efficient and comprehensive solutions to meet and satisfy your lab business needs.

#### System Edger SE-9090 Express

Provides High-Speed Automatic Edging & Polish Chamfering with High Precision and Accuracy

#### Auto Drilling Unit AHM-1000

Offers Automatic 3-D Drilling & Grooving for Various Lens Designs and Styles

#### Robotic Handling Unit RHU-1000/1500

Provides Robotic Handling for Automatic Lens Production



#### **High Efficiency & Versatility**

In a small footprint, NIDEK lab equipment offers highly efficient lens production --- A variety of lab configurations best suited for each customer's needs.

# Compact & Complete Systems of the SE-9090 Express & RHU-1000S





AES-1500

(SE-9090 Express & AHM-1000 & RHU-1500) includes Automatic Drilling & Grooving


**VCA Protocol** 

Lab networks using VCA protocol.

#### **Enhanced Flexibility**

Various configurations of the SE-9090 Express and RHU-1000CB can provide highly productive and efficient workflow of automated and continuous lens processing.

The systems are highly flexible for expansion, to fit in various floor layouts and production areas. Efficiency of output can be achieved without increasing manpower, offering high quality finished lenses with greater profitability.





# High Quality Automatic Crystal Cut™ Chamfering

The NIDEK System Edger SE-9090 Express offers automatic standard chamfering and polish chamfering; paying greater attention to the creation of more beautiful lenses with less effort than ever before.



Normal Chamfering Special Chamfering

# Faster Grinding with the Double Spindle System

The Double Spindle System incorporates a program to automatically control the grinding pressure of 7 different levels. As the grinding pressure is variable, time can be saved by processing at the best pressure and optimum speed.

## Simultaneous Double-Sided Shape Measurement

The SE-9090 Express simultaneously measures both front and rear sides of the lens for faster operation. The system measures a lens in approximately 5 seconds, providing accurate and fast processing.

# Improved Durability & Accuracy

The robust SE-9090 Express platform supports powerful, industrial-strength servo drive motors linked to an advanced RISC CPU microprocessor.

These drive the world's first patented dual-spindle edger, accurate to 0.15 mm in lens circumference. The powerful servo drive motors offer continuous operation capabilities, less down time and higher productivity.

# **High Quality Polishing**

The SE-9090 Express incorporates low-vibration motors for spindles, and 20,000 grinding control points for obtaining a high quality polished finish.

### **User Friendly Touch Panel**

The large 10.4-inch SVGA color LCD touch panel provides all the information needed for total processing. Bevel simulation can be observed, assuring a satisfying result.



10.4-inch SVGA color LCD (Touch Panel)

### **Advanced Networking Capability**

The SE-9090 Express is compatible with various communication protocols - VCA, RS-232C, LAN, etc., offering advanced networking capabilities.

#### **Data Transmission**

Data transmission with the barcode scanner (optional) can simplify troublesome procedures. This feature also saves processing time and reduces errors, to assure fast and high productivity.



Barcode Scanner (Optional)

# **Grinding Wheels**

T	Y	P	E	P	L	E


Lens material					Grinding					
Plastic	High index plastic	Polycar- bonate	Acrylic resin	Glass	Bevel edging	Flat (rimless) edging	Safety beveling	Bevel polishing	Flat (rimless) polishing	Safety bevel polishing
0	0	0	0	×	0	0	0	0	0	0

#### TYPE PLA


Lens material					Grinding					
Plastic	High index plastic	Polycar- bonate	Acrylic resin	Glass	Bevel edging	Flat (rimless) edging	Safety beveling	Bevel polishing	Flat (rimless) polishing	Safety bevel polishing
0	0	0	0	×	0	0	0	×	×	0

#### TYPE GLS


Lens material				Grinding						
Plastic	High index plastic	Polycar- bonate	Acrylic resin	Glass	Bevel edging	Flat (rimless) edging	Safety beveling	Bevel polishing	Flat (rimless) polishing	Safety bevel polishing
×	×	×	×	0	0	0	0	×	×	×




**Rough Process** 







Front & Rear Polish Chamfering



Front Polish Chamfering & Finishing




AHM-1000

# AHM-1000 Automatic Drilling and Grooving for Industrial Labs

The NIDEK Auto Drilling Unit AHM-1000 provides automatic hole drilling and grooving for various frame styles.

Combined with the RHU series, the AHM-1000 offers automatic and continuous lens processing for labs.



# RHU-1000/1500 Enhanced Functionality with the SE-9090 Express

The NIDEK Robotic Handling Unit (RHU) Series offer automatic lens conveyance to assist automation of the SE-9090 Express' lens processing in industrial labs.





## **Key Features**

- Small Foot Print
- High-Speed Conveyance 25 sec. / job (RHU-1000)
- Great Adaptability for any Style Edging Laboratory
- Easy Operation and Maintenance

# Auto Drilling Unit AHM-1000 Versatility

# **Key Features**

- Automatic 3-D Hole Drilling according to the Spherical Surface Curve of Lenses.

Peripheral Design Cut

- Progressive Grooving with Tilting Function for Rimless Frame Lenses
- 10.4-inch LCD Touch Panel for Easy Operation



3-D Drilling



**Grooving with Tilting Function** 

# Robotic Handling Unit RHU-1000/1500 Automation

The RHU-1000S (with stacker), RHU-1000CB (with conveyer belt) and RHU-1500 can provide continuous automatic processing to achieve high productivity and profits for large production labs. The RHU-1000 (without stacker/conveyer belt) is also an available option.



SE-9090 Express & RHU-1000S (NIDEK Tray Type Stacker)\*

\*LOH tray type stacker is also available.



SE-9090 Express & RHU-1000CB (with Conveyer Belt)



AES-1500\* (RHU-1500)
\*AES-1500 is the combined system of the

SE-9090 Express + AHM-1000 + RHU-1500.